

# Eaton CHB260

Catalog Number: CHB260

Eaton CH thermal magnetic circuit breaker, 70 A, 10 kAIC, Two-pole, 120/240 V, #8-2 AWG, CHB, CH Loadcenters



## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton CH thermal magnetic circuit breaker | CHB260                |
|   | <b>UPC</b>            |
|   | 782113112527          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.4 in                                    | 2.7 in                |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 1.5 in                                    | 0.55 lb               |
| <b>Warranty</b>                           | <b>Certifications</b> |
| Limited lifetime                          | UL 489                |
|   | Contact Manufacturer  |

## defaultTaxonomyAttributeLabel

### Type

Circuit breaker

### Amperage Rating

60 A

### Voltage rating

120/240 V

### Circuit breaker type

CHB

### Used with

CH Loadcenters

### Interrupt rating

10 kAIC

### Wire size

#8-2 AWG

### Number of poles

Two-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Catalogs

[Eaton's Volume 12—Aftermarket, Renewal Parts and Life Extension Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHB260](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)