

Eaton CH thermal magnetic circuit breaker

CHF120

UPC:786685361840

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** .75 IN

Weight:.28 LB

Notes:Switching Duty Rated, HACR Rated, Single-Pole Requires One 3/4-Inch Space, With Trip Indication.

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Type:** Type CHF 3/4-Inch standard circuit breaker
- **Amperage Rating:** 20A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** CHF
- **Trip Type:** Trip flag
- **Wire Size:** (1) #14-8 AWG, (2) #14-10 AWG Cu/Al
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eatons CHF Circuit Breaker with Trip Flag](#)
- [Eaton Specification Sheet - CHF120](#)

Certifications:

- UL 489

Product compliance:

- HACR Rated

© 2016 Eaton. All rights reserved.