

Eaton CHF120ST

Catalog Number: CHF120ST

Eaton Type CHF 3/4-inch Standard Circuit Breaker, Single-Pole, 20A, 120/240V, 10 kAIC, (1) #14-8, (2) #14-10 AWG Cu/Al 60°C or 75°C, Shunt Trip



General specifications

Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CHF120ST
	UPC
	786685384818
Product Length/Depth	Product Height
4.8 in	3.5 in
Product Width	Product Weight
3.5 in	0.55 lb
Warranty	Certifications
Limited lifetime residential, 1 year commercial	UL 489
	Catalog Notes
	Switching Duty Rated, HACR Rated, Single-Pole Requires One 2/4-Inch Space, With Trip Indication.

Type

Type CHF 3/4-inch Standard Circuit Breaker

Special features

Shunt Trip

Amperage Rating

20 A

Voltage rating

120/240 V

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CH

Wire size

(1) #14-8 AWG

(2) #14-10 AWG Cu/Al

Number of poles

Single-pole

Brochures

Type CH Circuit Breakers and Loadcenters

Eaton's CHF Circuit Breaker with Trip Flag

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHF120ST



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia