

Eaton CH thermal magnetic circuit breaker

CHF150

UPC:786685532141

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** .75 IN

Weight:.25 LB

Notes:HACR Rated, Single-Pole Requires One 2/4-Inch Space, With Trip Indication.

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Type:** Type CHF 3/4-Inch standard circuit breaker
- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** CHF
- **Trip Type:** Trip flag
- **Wire Size:** #14-2 AWG Cu/Al
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eatons CHF Circuit Breaker with Trip Flag](#)
- [Eaton Specification Sheet - CHF150](#)

Certifications:

- UL 489

Product compliance:



- HACR Rated

© 2016 Eaton. All rights reserved.