

Eaton CHF150

Catalog Number: CHF150

Eaton CH thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 50 A, 10 kAIC, Single-pole, 120/240V, CHF, Trip flag, common breaker trip, #14-2 AWG Cu/Al, CHF, Type CH Loadcenters



General specifications

Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CHF150
	UPC
	786685532141
Product Length/Depth	Product Height
3 in	3 in
Product Width	Product Weight
0.75 in	0.25 lb
Warranty	Compliances
Limited lifetime residential, 1 year commercial	HACR Rated
	Certifications
	UL 489

Catalog Notes

HACR Rated, Single-Pole Requires One 2/4-Inch Space, With Trip Indication.

defaultTaxonomyAttributeLabel

Type

Type CHF 3/4-Inch standard circuit breaker

Amperage Rating

50 A

Voltage rating

120/240 V

Trip Type

Trip flag

Circuit breaker type

CHF

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CHF

Wire size

#14-2 AWG Cu/Al

Number of poles

Single-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type CH Circuit Breakers and Loadcenters](#)

[Eaton's CHF Circuit Breaker with Trip Flag](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHF150](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)