

# Eaton CHF225

Catalog Number: CHF225

Eaton CH thermal magnetic circuit breaker, Type CHF 3/4-Inch standard circuit breaker, 25 A, 10 kAIC, Two-pole, 120/240V, CHF, Trip flag, common breaker trip, (1) #14-8 AWG, (2) #14-10 AWG Cu/Al, CHF, Type CH Loadcenters



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH thermal magnetic circuit breaker	CHF225
	UPC
	786685361895
<b>Product Length/Depth</b>	<b>Product Height</b>
1.5 in	2.6 in
<b>Product Width</b>	<b>Product Weight</b>
0.75 in	0.5 lb
<b>Warranty</b>	<b>Compliances</b>
Limited lifetime residential, 1 year commercial	HACR Rated
	<b>Certifications</b>
	UL 489

## Catalog Notes

HACR Rated. Two-Pole 120/240V  
Common Trip Requires Two 3/4-Inch  
Spaces. With Trip Indication

## defaultTaxonomyAttributeLabel

### Type

Type CHF 3/4-Inch standard circuit breaker

### Amperage Rating

25 A

### Voltage rating

120/240 V

### Trip Type

Trip flag

### Circuit breaker type

CHF

### Used with

Type CH Loadcenters

### Interrupt rating

10 kAIC

### Main circuit breaker

CHF

### Wire size

(1) #14-8 AWG

(2) #14-10 AWG Cu/Al

### Number of poles

Two-pole

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

[Type CH Circuit Breakers and Loadcenters](#)

[Eaton's CHF Circuit Breaker with Trip Flag](#)

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHF225](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)