

Eaton CH thermal magnetic circuit breaker

CHF230

UPC:786685361901

Dimensions:

- **Height:** 2.6 IN
- **Length:** 1.5 IN
- **Width:** .75 IN

Weight: .28 LB

Notes: HACR Rated. Two-Pole 120/240V Common Trip Requires Two 3/4-Inch Spaces. With Trip Indication

Warranties:

- Limited lifetime residential, 1 year commercial

Specifications:

- **Type:** Type CHF 3/4-Inch standard circuit breaker
- **Amperage Rating:** 30A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** CHF
- **Trip Type:** Trip flag
- **Wire Size:** (1) #14-8 AWG, (2) #14-10 AWG Cu/Al
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eatons CHF Circuit Breaker with Trip Flag](#)
- [Eaton Specification Sheet - CHF230](#)

Certifications:



- UL 489

Product compliance:

- HACR Rated

© 2016 Eaton. All rights reserved.