



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHF245 Type CHF BRKR 45A/2P 120/240V 10kaic *Eaton Corp*

Catalog Number	CHF245
Manufacturer	Eaton Corp
Description	CH Style Load Center, 45 A, 120/240 V, #14 to #1 Awg Wire Size, 0.5 LB
Weight per unit	0.5000 (lbs/each)
Product Category	Single Phase Main Breaker Load

Features

dimensions	1.5000 IN X 3.2000 IN X 2.6000 IN
interrupt rating	10 kAIC
Poles	Two-pole
Trip Type	Trip flag

Descriptions

Description	TYPE CHF BRKR 45A/2P 120/240V 10KAIC
extra long description	ETN CHF245 CHF BREAKER, 45A / 2P 12
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous

Manufacturer Information

GTIN	00786685545615
UPC	786685545615

Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Package	25
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489,HACR Rated