

Eaton CHM9N9NS

Catalog Number: CHM9N9NS

Eaton pedestal mount metered, Water and tamper resistant left/center receptacle, Metered-ring, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GF, NEMA 5-20R2GFI

Photo is representative

General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHM9N9NS
UPC	Product Length/Depth
786676013246	7.25 in
Product Height	Product Width
31 in	10 in
Product Weight	Warranty
30 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL 231	
UL Listed file E163588	



Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA 5-20R2GF

Receptacle left

NEMA 5-20R2GFI

Receptacle right

None

Type

Metered-ring

Miscellaneous

Special features

Water and tamper resistant left/center receptacle

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CHM9N9NS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia