Eaton CHN240GF

Catalog Number: CHN240GF

Eaton CH GFCI circuit breaker,Plug-in circuit breaker,40 A,10 kAIC,Two-pole,120/240 V,CH,Common,GFI,5 mA

Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH GFCI circuit breaker	CHN240GF
UPC	Product Length/Depth
786689217266	6 in
Product Height	Product Width
2.25 in	3.5 in
Product Weight	Certifications
0.8 lb	UL 489



defaultTaxonomyAttributeLabel

Туре

Plug-in circuit breaker

Amperage Rating

40 A

Voltage rating

120/240 V

Trip Type

Common

Indicators

GFI

Protection

5 mA

Interrupt rating

10 kAIC

Main circuit breaker

СН

Number of poles

Two-pole



Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets Eaton Specification Sheet - CHN240GF



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia