

Eaton CHP08N200RF

Catalog Number: CHP08N200RF

Eaton CH convertible loadcenters, Cover included, Convertible (main device purchased separately), 200 A, X5,Copper, NEMA 3R, Metallic, CSR, 16, 8, Three-wire, Single-phase, Overhead

General specifications



Photo is representative

Product Name

Eaton CH convertible loadcenter

UPC

786689058487

Product Height

5.19 in

Product Weight

26 lb

Certifications

UL 67

UL 50

Catalog Number

CHP08N200RF

Product Length/Depth

29 in

Product Width

14.31 in

Warranty

Limited lifetime

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Convertible (main device purchased separately)

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

16

Number of spaces

8

Phase

Single-phase

Feed type

Overhead

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP08N200RF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)