

Eaton CHP12L125R

Catalog Number: CHP12L125R

Eaton CH main lug loadcenters,Cover included,Main Lug Only,125A,X0,Copper,NEMA 3R,Metallic,Overhead,24,12,Three-wire,Single-phase



Photo is representative

General specifications

| | |
|------------------------------|--|
| Product Name | Catalog Number |
| Eaton CH main lug loadcenter | CHP12L125R |
| UPC | Product Length/Depth |
| 786689058494 | 16.75 in |
| Product Height | Product Width |
| 5.19 in | 14.31 in |
| Product Weight | Warranty |
| 18 lb | Limited lifetime |
| Certifications | Catalog Notes |
| UL 67 | Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs. |
| UL 50 | |

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Main Lug Only

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Number of circuits

24

Number of spaces

12

Phase

Single-phase

Box size

X0

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP12L125R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia