

Eaton CHP12L125R

Catalog Number: CHP12L125R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 125A, X0, Copper, NEMA 3R, Metallic, Overhead, 24, 12, Three-wire, Single-phase



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP12L125R
UPC	Product Length/Depth
786689058494	16.75 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
18 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Main Lug Only

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Number of circuits

24

Number of spaces

12

Phase

Single-phase

Box size

X0

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP12L125R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)