


Eaton CHP16L125X1

Catalog Number: CHP16L125X1

Eaton CH main lug loadcenters,PON,CH,125A,X1,Copper,!,NEMA 1 indoor,Steel,25 kAIC,32,Single-pole,16,Three-wire,Single-phase,120/240 V,#6-2/0 AWG



General specifications

| | |
|------------------------------|-----------------------------------|
| Product Name | Catalog Number |
| Eaton CH main lug loadcenter | CHP16L125X1 |
| UPC | Product Length/Depth |
| 786689059705 | 18.75 in |
| Product Height | Product Width |
| 4 in | 14.3 in |
| Product Weight | Warranty |
| 9.9 lb | Limited lifetime |
| Certifications | Catalog Notes |
| UL 50 UL 67 | Purchase Size X1 cover seperately |

defaultTaxonomyAttributeLabel

Special features

PON

Type

CH

Amperage Rating

125 A

Bus material

Copper

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#8-1/0 AWG Cu

Box size

X1

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP16L125X1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)