

Eaton CHP22B100R

Catalog Number: CHP22B100R

Eaton CH main breaker loadcenters,Cover included,Main breaker,100 A,X2,Copper,NEMA 3R,Metallic,CH,44,22,Three-wire,Single-phase,Overhead,120/240 V

Photo is representative

General specifications

Product Name

Eaton CH main breaker loadcenter

Catalog Number

CHP22B100R

UPC

786689058562

Product Length/Depth

21 in

Product Height

5.19 in

Product Width

14.31 in

Product Weight

22 lb

Warranty

Limited lifetime

Certifications

UL 50

UL 67

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.



defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Main circuit breaker

CH

Number of circuits

44

Number of spaces

22

Phase

Single-phase

Feed type

Overhead

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP22B100R](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)