

# Eaton CHP22N125X2

Catalog Number: CHP22N125X2

Eaton CH PON 3/4-inEaton CH loadcenter, 125A, convertible, 22 spaces



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP22N125X2
UPC	Product Length/Depth
786679189726	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
11.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 50	Purchase Size X2 Cover Separately
UL 67	

## defaultTaxonomyAttributeLabel

### Type

Convertible

### Amperage Rating

125 A

### Bus material

Copper

### Cover

X2

### Feed type

Top/bottom

### Number of circuits

22

### Number of spaces

22

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

X2

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP22N125X2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHP22N125X2

Catalog Number: CHP22N125X2

Eaton CH PON 3/4-inEaton CH loadcenter, 125A, convertible, 22 spaces



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP22N125X2
UPC	Product Length/Depth
786679189726	21 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
11.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 50	Purchase Size X2 Cover Separately
UL 67	

## defaultTaxonomyAttributeLabel

### Type

Convertible

### Amperage Rating

125 A

### Bus material

Copper

### Cover

X2

### Feed type

Top/bottom

### Number of circuits

22

### Number of spaces

22

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

X2

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP22N125X2](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)