

# Eaton CHP24B200X5

Catalog Number: CHP24B200X5

Eaton CH main breaker loadcenters, PON, Main breaker, 200 A, X5, Copper, X5, NEMA 1, Metallic, 10 kAIC, CSR, 48, 24, Three-wire, Single-phase, #2 AWG-300 kcmil, 120/240 V



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CHP24B200X5
<b>UPC</b>	<b>Product Length/Depth</b>
786679189580	29 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
17.5 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Purchase Size X5 Cover Separately

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main breaker

### Amperage Rating

200 A

### Bus material

Copper

### Cover

X5

### Main circuit breaker

CSR

### Number of circuits

48

### Number of spaces

24

### Phase

Single-phase

### Wire size

#2 AWG-300 kcmil

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP24B200X5](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)