Specifications



Photo is representative





Eaton CHP24L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 48, 24, Three-wire, Single-phase

General specifications		
PRODUCT NAME	Eaton CH main lug loadcenter	
CATALOG NUMBER	CHP24L150R	
UPC	786689058623	
PRODUCT LENGTH/DEPTH	29 in	
PRODUCT HEIGHT	5.19 in	
PRODUCT WIDTH	14.31 in	
PRODUCT WEIGHT	26 lb	
WARRANTY	Limited lifetime	
CERTIFICATIONS	UL 67 UL 50	
CATALOG NOTES	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.	



Product specifications		
SPECIAL FEATURES	Cover included	
ТҮРЕ	Main Lug Only	
AMPERAGE RATING	150 A	
BUS MATERIAL	Copper	
FEED TYPE	Overhead	
NUMBER OF CIRCUITS	48	
NUMBER OF SPACES	24	
PHASE	Single-phase	
BOX SIZE	X5	
ENCLOSURE	NEMA 3R	
ENCLOSURE MATERIAL	Metallic	
INTERRUPT RATING	25 kAIC	
NUMBER OF WIRES	3	

Resources	
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CHP24L150R
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com



information.



latest product and support

Follow us on social media to get the



