

# Eaton CHP24L150X5

Catalog Number: CHP24L150X5

Eaton CH main lug only panel, PON,150A,X5,Copper bus,,NEMA 1 indoor,Steel,10 kAIC,48 circuits,24 spaces,Single-phase,120/240 V,#4 AWG-300 kcmil



## General specifications

Product Name	Catalog Number
Eaton CH spa panel	CHP24L150X5
UPC	Product Length/Depth
786689054274	29 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
15.4 lb	UL 67

## Catalog Notes

Purchase Size X5 Cover Separately

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

CH

### Amperage Rating

150 A

### Bus material

Copper

### Number of circuits

48

### Number of spaces

24

### Phase

Single-phase

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Steel

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP24L150X5](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)