Eaton CHP30B100R

Catalog Number: CHP30B100R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 100 A, X5, Copper, NEMA 3R, Metallic, CH, 60, 30, Three-wire, Single-phase, Overhead, 120/240 V

General specifications

Product Name

Eaton CH main breaker loadcenter

UPC

786689058647

Product Height

5.19 in

Product Weight

26 lb

Certifications

UL 50 UL 67 Catalog Number

CHP30B100R

Product Length/Depth

29 in

Product Width

14.31 in

Warranty

Limited lifetime

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates.

For rainproof hubs.



Photo is representative



default Taxonomy Attribute Label

Special features

Cover included

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Main circuit breaker

СН

Number of circuits

60

Number of spaces

30

Phase

Single-phase

Feed type

Overhead

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP30B100R



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia