

# Eaton CHP30B125R

Catalog Number: CHP30B125R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 125 A, X5, Copper, NEMA 3R, Metallic, CH, 60, 30, Three-wire, Single-phase, Overhead, 120/240 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CHP30B125R
<b>UPC</b>	<b>Product Length/Depth</b>
786689058654	29 in
<b>Product Height</b>	<b>Product Width</b>
5.19 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
26 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

## defaultTaxonomyAttributeLabel

### Special features

Cover included

### Type

Main breaker

### Amperage Rating

125 A

### Bus material

Copper

### Main circuit breaker

CH

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Feed type

Overhead

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP30B125R](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)