

# Eaton CHP30B125X5

Catalog Number: CHP30B125X5

Eaton CH main breaker loadcenters,PON,Main breaker,125 A,X5,Copper,X5,NEMA 1,Metallic,10 kAIC,CH,60,30,Three-wire,Single-phase,#6-1/0 AWG,120/240 V



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP30B125X5
UPC	Product Length/Depth
786679189603	29 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15.6 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Purchase Size X5 Cover Separately
UL 50	

## defaultTaxonomyAttributeLabel

### Special features

PON

### Type

Main breaker

### Amperage Rating

125 A

### Bus material

Copper

### Cover

X5

### Main circuit breaker

CH

### Number of circuits

60

### Number of spaces

30

### Phase

Single-phase

### Wire size

#6-1/0 AWG

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHP30B125X5](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)