Eaton CHP32B150R

Catalog Number: CHP32B150R

Eaton CH main breaker loadcenters, Cover included, Main breaker, 150 A, X5, Copper, NEMA 3R, Metallic, CSR, 64, 32, Three-wire, Single-phase, Overhead, 120/240 V

General specifications



Product Name

Eaton CH main breaker loadcenter

UPC

786689058661

Product Height

5.19 in

Product Weight

26 lb

Certifications

UL 50

UL 67

Catalog Number

CHP32B150R

Product Length/Depth

29 in

Product Width

14.31 in

Warranty

Limited lifetime

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

Photo is representative



default Taxonomy Attribute Label

Special features

Cover included

Type

Main breaker

Amperage Rating

150 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

64

Number of spaces

32

Phase

Single-phase

Feed type

Overhead

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP32B150R



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia