

Eaton CHP32B150X6

Catalog Number: CHP32B150X6

Eaton CH main breaker loadcenters, Main breaker, 150 A, X6, Copper, X6, NEMA 1, Metallic, 25 kAIC, CSR, 64, Single-pole, 32, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP32B150X6
UPC	Product Length/Depth
786689055165	34.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
19.9 lb	Limited lifetime
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Main breaker

Amperage Rating

150 A

Bus material

Copper

Cover

X6

Main circuit breaker

CSR

Number of circuits

64

Number Of Poles

Single-pole

Number of spaces

32

Phase

Single-phase

Wire size

#6-1/0 AWG

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP32B150X6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)