

Eaton CHP32E225X6

Catalog Number: CHP32E225X6

Eaton CH 3/4-in Eaton CH loadcenter, 225A, convertible w/ lugs, 32 spaces



General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP32E225X6
UPC	Product Length/Depth
786689055189	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
17.8 lb	Limited lifetime
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Convertible, Main Lugs Installed

Amperage Rating

225 A

Bus material

Copper

Cover

X6

Feed type

Top/bottom

Number of circuits

64

Number Of Poles

Single-pole

Number of spaces

32

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#6-1/0 AWG

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP32E225X6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)