

Eaton CHP32N225X6

Catalog Number: CHP32N225X6

Eaton CH plug-on neutral loadcenter, 225A, convertible, 32 spaces



General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP32N225X6
UPC	Product Length/Depth
786689055196	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
17.7 lb	Limited lifetime
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

225 A

Bus material

Copper

Cover

X6

Feed type

Top/bottom

Number of circuits

64

Number Of Poles

Single-pole

Number of spaces

32

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#6-1/0 AWG

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP32N225X6](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)