

Eaton CHP42L225

Catalog Number: CHP42L225

Eaton CH main lug loadcenters,PON,Main Lug Only,225A,X6,Copper,Cover included,NEMA 1 indoor,Metallic,10 kAIC,84,Single-pole,42,Two hots, a neutral and a ground,Single-phase,120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP42L225
UPC	Product Length/Depth
786689054618	35.8 in
Product Height	Product Width
5 in	15.9 in
Product Weight	Warranty
31.25 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Retail Packaging
UL 50	

defaultTaxonomyAttributeLabel

Special features

PON

Type

Main Lug Only

Amperage Rating

225 A

Bus material

Copper

Cover

Cover included

Number of circuits

84

Number Of Poles

Single-pole

Number of spaces

42

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#1 AWG-300 kcmil

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP42L225](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)