Eaton CHP42L225R

Catalog Number: CHP42L225R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 225A, X6, Copper, NEMA 3R, Metallic, Overhead, 84, 42, Three-wire, Single-phase

General specifications

Product Name

Eaton CH main lug loadcenter

UPC

786689058739

Product Height

5.19 in

Product Weight

28 lb

Certifications

UL 50 UL 67 Catalog Number

CHP42L225R

Product Length/Depth

34 in

Product Width

14.31 in

Warranty

Limited lifetime

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.





default Taxonomy Attribute Label

Special features

Cover included

Type

Main Lug Only

Amperage Rating

225 A

Bus material

Copper

Feed type

Overhead

Number of circuits

84

Number of spaces

42

Phase

Single-phase

Box size

X6

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Loadcenters and Circuit Breakers

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CHP42L225R



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia