

Eaton CHPX0AF

Catalog Number: CHPX0AF

Eaton CH Indoor Combination Cover, Flush-mount applications, Type CH indoor combination cover, 125 A, X0, Sandlewood, NEMA 1, CH, Flush, 12 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH cover	CHPX0AF
UPC	Product Length/Depth
786689162269	17.75 in
Product Height	Product Width
0.5 in	15.31 in
Product Weight	Warranty
6 lb	Limited lifetime
Certifications	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Special features

Flush-mount applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Flush

Number of spaces

12

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X0

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX0AF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)