

# Eaton CHPX1AF

Catalog Number: CHPX1AF

Eaton CH Indoor Combination Cover, Flush-mount applications, Type CH indoor combination cover, 100 A, X1, Sandlewood, NEMA 1, CH, Flush, 16 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V



## General specifications

Product Name	Catalog Number
Eaton CH cover	CHPX1AF
UPC	Product Length/Depth
786689162290	1 in
Product Height	Product Width
19.75 in	15.31 in
Product Weight	Warranty
6.7 lb	Limited lifetime
Certifications	
Contact Manufacturer	

## defaultTaxonomyAttributeLabel

### Special features

Flush-mount applications

### Type

Cover

### Amperage Rating

225 A

### Bus material

Aluminum

### Mounting

Flush

### Number of spaces

16

### Phase

Three-phase

### Used with

CH Breakers

### Voltage rating

120/240 V

### Box size

X1

### Color

Sandalwood

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

CH - 3/4 in - plug on neutral

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHPX1AF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)