

Eaton CHPX5LS

Catalog Number: CHPX5LS

Eaton CH Surface Cover, Surface or flush universal applications, Type CH surface cover, 150 A, X5, Sandlewood, NEMA 1, CH, Surface, flush, 32 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH cover	CHPX5LS
UPC	Product Length/Depth
786689162382	1 in
Product Height	Product Width
29.12 in	14.31 in
Product Weight	Warranty
9.8 lb	Limited lifetime
Certifications	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Special features

Surface or flush universal applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Surface, flush

Number of spaces

32

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X5

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX5LS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)