

# Eaton CHPX6BF

Catalog Number: CHPX6BF

Eaton CH Combination Cover, Flush-mount applications, Type CH combination cover, 150 A, X6, Sandlewood, NEMA 1, CH, Flush, 32 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

## General specifications



Photo is representative

### Product Name

Eaton CH cover

### UPC

786689162399

### Product Height

35.12 in

### Product Weight

11.8 lb

### Certifications

Contact Manufacturer

### Catalog Number

CHPX6BF

### Product Length/Depth

1 in

### Product Width

15.31 in

### Warranty

Limited lifetime

## defaultTaxonomyAttributeLabel

### Special features

Flush-mount applications

### Type

Cover

### Amperage Rating

225 A

### Bus material

Aluminum

### Mounting

Flush

### Number of spaces

32

### Phase

Three-phase

### Used with

CH Breakers

### Voltage rating

120/240 V

### Box size

X6

### Color

Sandalwood

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

CH - 3/4 in - plug on neutral

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CHPX6BF



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)