

# Eaton CHPX9BF

Catalog Number: CHPX9BF

Eaton CH Indoor Combination Cover, Flush-mount applications, Type CH indoor combination cover, 200 A, X9, Sandlewood, NEMA 1, CH, Flush, 60 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

## General specifications



**Product Name**  
Eaton CH cover

**UPC**  
786689162238

**Product Height**  
46 in

**Product Weight**  
15.5 lb

**Certifications**

**Contact Manufacturer**

**Catalog Number**  
CHPX9BF

**Product Length/Depth**  
1 in

**Product Width**  
15.31 in

**Warranty**  
Limited lifetime

## defaultTaxonomyAttributeLabel

### Special features

Flush-mount applications

### Type

Cover

### Amperage Rating

225 A

### Bus material

Aluminum

### Mounting

Flush

### Number of spaces

60

### Phase

Three-phase

### Used with

CH Breakers

### Voltage rating

120/240 V

### Box size

X9

### Color

Sandalwood

### Enclosure

NEMA 1

### Interrupt rating

10 kAIC

### Size

CH - 3/4 in - plug on neutral

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHPX9BF](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)