

Eaton CHPX9NF

Catalog Number: CHPX9NF

Eaton CH Indoor Combination Cover, Flush-mount applications, Type CH indoor combination cover, 225 A, X9, Sandlewood, NEMA 1, CH, Flush, 60 Spaces, CH - 0.75 in - Plug On Neutral, CH Breakers, 120/240 V

General specifications



Photo is representative

Product Name	Catalog Number
Eaton CH cover	CHPX9NF
UPC	Product Length/Depth
786689162252	1 in
Product Height	Product Width
46 in	15.31 in
Product Weight	Warranty
15.5 lb	Limited lifetime
Certifications	
Contact Manufacturer	

defaultTaxonomyAttributeLabel

Special features

Flush-mount applications

Type

Cover

Amperage Rating

225 A

Bus material

Aluminum

Mounting

Flush

Number of spaces

60

Phase

Three-phase

Used with

CH Breakers

Voltage rating

120/240 V

Box size

X9

Color

Sandalwood

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

CH - 3/4 in - plug on neutral

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHPX9NF](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)