



## Eaton Classified 3/4" thermal magnetic circuit breaker

**CHQ150**

**UPC:**782113010885

### Dimensions:

- **Height:** 3 IN
- **Length:** 2.5 IN
- **Width:** .8 IN

**Weight:**.3 LB

**Notes:**Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.

### Warranties:

- Limited lifetime residential, 1 year commercial

### Specifications:

- **Type:** Type CHQ 3/4-Inch classified replacement breaker clamshell pack
- **Special Features:** Ground fault
- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** CHQ
- **Wire Size:** (1) #14-8 AWG, (2) #14-10 AWG Cu/Al
- **Quantity:** Q30
- **Circuit Breaker Type:** CH
- **Used With:** Type CH Loadcenters

### Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHQ150](#)

### Certifications:

- UL 489

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.