



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CHQ240 Type CHQ Classified BRKR 40A/2 Pole 120/240V 10K *Eaton Corp*

Catalog Number	CHQ240
Manufacturer	Eaton Corp
Description	Standard Trip Circuit Breaker, 40 A, Common Tripping Mechanism, Line and Load Lug Terminal, Plug-On, 240 V Ac, 3 In Overall Height, 2.5 In Overall Length, 1.5 In Overall Width, 0.60 LB
Weight per unit	0.6000 (lbs/each)
Product Category	2 Pole Standard Trip Plug-In

Features

amperage rating	40 A
dimensions	2.5000 IN X 1.5000 IN X 3.0000 IN
Poles	Two-pole
Trip Type	Common breaker trip

Descriptions

Description	TYPE CHQ CLASSIFIED BRKR 40A/2 POLE 120/240V 10K
extra long description	ETN CHQ240 CHQ Classified 40A/2 Pol
Special Features	Ground fault

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113010946
UPC	782113010946

Taxonomies, Classifications, and Categories

Category Description	CLASSIFIED BREAKERS
Type	3/4" Thermal magnetic circuit breakers

Packaging

Carton	1
Package	5
Weight Per each	0.6

Uses, Certifications, and Standards

Application	Marine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedGeneration - Renewable Energy - Alternative Energy
standard	UL 489