

Eaton CHR1G7N7NSU

Catalog Number: CHR1G7N7NSU

Eaton pedestal mount metered, Pos 1: Gnd fault, Pos 2: Non-gnd fault, Pos 3: Non-gnd fault, Bottom, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 14-50R, Right: NEMA 5-20R2GFI, Ringless



Photo is representative

General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHR1G7N7NSU
UPC	Product Length/Depth
782116153367	31 in
Product Height	Product Width
8 in	10 in
Product Weight	Warranty
24 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588
UL 231

Physical Attributes

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Feed type

Bottom

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 14-50R

Receptacle right

NEMA 5-20R2GFI

Type

Metered-ringless

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHR1G7N7NSU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)