

# Eaton CHR7N7N5GSU

Catalog Number: CHR7N7N5GSU

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Gnd fault, Bottom, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 5-20R2GFI, Right: NEMA 6-20R2, Ringless



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton pedestal mount metered	CHR7N7N5GSU
<b>UPC</b>	<b>Product Length/Depth</b>
782116153312	31 in
<b>Product Height</b>	<b>Product Width</b>
8 in	10 in
<b>Product Weight</b>	<b>Warranty</b>
24 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

## Certifications

UL 231  
UL Listed file E163588

## Physical Attributes

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Ground fault

### Feed type

Bottom

### Mounting

Surface

### Number of circuits

4

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 5-20R2GFI

### Receptacle right

NEMA 6-20R2

### Type

Metered-ringless

## Resources

### Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

### Specifications and datasheets

[Eaton Specification Sheet - CHR7N7N5GSU](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)