

Eaton CHR7N7N5GSUG

Catalog Number: CHR7N7N5GSUG

Eaton pedestal mount metered, Pos 1: Non-gnd fault, Pos 2: Non-gnd fault, Pos 3: Gnd fault, Painted green, Bottom, Surface, Circuits: 4, Center: NEMA 5-20R2GFI, Left: NEMA 5-20R2GFI, Right: NEMA 6-20R2, Ringless



General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHR7N7N5GSUG
UPC	Product Length/Depth
782116339631	5 in
Product Height	Product Width
5 in	10 in
Product Weight	Warranty
15 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL 231
UL Listed file E163588

defaultTaxonomyAttributeLabel

Type

Metered-ringless

Color

Painted green

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Ground fault

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 5-20R2GFI

Receptacle right

NEMA 6-20R2

Feed type

Bottom

Mounting

Surface

Number of circuits

4

Resources

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHR7N7N5GSUG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)