



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHR9N9NKGS Pop TF RL 20/20/20 *Eaton Corp*

Catalog Number	CHR9N9NKGS
Manufacturer	Eaton Corp
Description	Eaton Pedestal Mount Metered, Top, Surface, Circuits: 4, Weather-Resist and Tamper Resist Center and Left Receptacle, Weather Resist Right Receptacle, Center: Nema 5-20R2GFI WR TR, Left: Nema 5-20R2GFI WR TR, Right: Nema 6-20R2 WR, Ringless
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

### Features

dimensions	30.0000 IN X 9.0000 IN X 6.5000 IN
Mounting Type	Surface

### Dimensions and Weight

Height	6.5000
Length	30.0000
Width	9.0000

### Descriptions

Description	POP TF RL 20/20/20
extra long description	ETN CHR9N9NKGS POP, TF, RL, 20/20/2
Features	Eaton's temporary power panels provide safe, reliable power for RV and construction sites. Durable, long-lasting units are available as metered (ring or ringless) or unmetered and can be mounted at the surface, on a pedestal, or in a back-to-back configuration.
Long Description	Eaton pedestal mount metered, Top, Surface, Circuits: 4, Weather-resist and tamper resist center and left receptacle, weather resist right receptacle, Center: NEMA 5-20R2GFI WR TR, Left: NEMA 5-20R2GFI WR TR, Right: NEMA 6-20R2 WR, Ringless
Product Type	Pop, TF, RL, 20/20/20

### Manufacturer Information

Brand	Eaton Corp
GTIN	00786680193606
Manufacturers Part Number	CHR9N9NKGS
UPC	786680193606

### Taxonomies, Classifications, and Categories

Category Description	RV Power Pedestals
Type	Pedestal mount metered



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	30

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs
Mounting	SURFACE
standard	UL 231,UL Listed file E163588