

Eaton CHR9N9NKGSU

Catalog Number: CHR9N9NKGSU

Eaton pedestal mount metered, Ringless, Left/Pos 1: NEMA TT-30R Non-grd fault, Center/Pos 2: NEMA 5-20R2GFI Non-grd fault WR/TR, Right/Pos 3: None, Top, Surface mounted, Standard 4 circuit



Photo is representative

General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHR9N9NKGSU
UPC	Product Length/Depth
786689321475	8 in
Product Height	Product Width
31 in	10 in
Product Weight	Certifications
24 lb	UL 231
	UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Receptacle center

NEMA TT-30R

Receptacle left

NEMA 5-20R2GFI

Type

Ringless

Miscellaneous

Special features

Pedestal mount metered

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHR9N9NKGSU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)