

# Eaton CHR9N9NKGSUG

Catalog Number: CHR9N9NKGSUG

Eaton pedestal mount metered, Ringless, Left/Pos 1: 5-20R2GFI Non-grd fault WR/TR, Center/Pos 2: 5-20R2GFI Non-grd fault WR/TR, Right/Pos 3: 6-20R2 Grd fault WR, Bottom Fed, Surface mounted, Standard 4 circuit



## General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHR9N9NKGSUG
UPC	Product Length/Depth
786689321482	8 in
Product Height	Product Width
31 in	10 in
Product Weight	Certifications
24 lb	UL 231
	UL Listed file E163588

## defaultTaxonomyAttributeLabel

### Special features

Pedestal mount metered

### Type

Ringless

### Circuit breaker position 1

Non-ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Ground fault

### Receptacle center

NEMA5-20R2GFI

### Receptacle left

NEMA5-20R2GFI

### Receptacle right

NEMA6-20R2

### Feed type

Bottom

### Mounting

Surface

### Number of circuits

4

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - CHR9N9NKG5UG](#)