

Eaton CHR9N9NKNS

Catalog Number: CHR9N9NKNS

Eaton pedestal mount metered, Ringless, Left/Pos 1: 5-20R2GFI Non-grd fault WR/TR, Center/Pos 2: 5-20R2GFI Non-grd fault WR/TR, Right/Pos 3: 6-20R2 Grd fault WR, Top, Surface mounted, 6 circuit



General specifications

Product Name	Catalog Number
Eaton pedestal mount metered	CHR9N9NKNS
UPC	Product Length/Depth
786689321505	6.8 in
Product Height	Product Width
7.5 in	9.5 in
Product Weight	Certifications
26 lb	UL 231
	UL Listed file E163588

Physical Attributes

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Ground fault

Feed type

Top

Mounting

Surface

Number of circuits

6

Receptacle center

NEMA5-20R2GFI

Receptacle left

NEMA5-20R2GFI

Receptacle right

NEMA6-20R2

Type

Ringless

Miscellaneous

Special features

Pedestal mount metered

Resources

Specifications and datasheets

[Eaton Specification Sheet - CHR9N9NKNS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia