



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CHR9N9NS Pop, Ringless, (2) 5-20R2GFI Receptacles, Eaton Corp

Catalog Number	CHR9N9NS
Manufacturer	Eaton Corp
Description	
Weight per unit	30.0 (lbs/each)
Product Category	Metered Power Outlet Pedestals

### Features

circuit breaker position 1	Non-ground fault
circuit breaker position 2	Non-ground fault
circuit breaker position 3	None Mount
dimensions	77.4700centimetreX25.4000centimetreX17.7800centimetre
feed type	Top
Number of Circuits	4 in
receptacle center	NEMA 5-20R2GF
receptacle left	NEMA 5-20R2GFI
receptacle right	None Mount

### Descriptions

Description	POP, RINGLESS, (2) 5-20R2GFI RECEPTACLES,
Product Type	Pop Ringless (2) 5-20R2GFI Receptacles
Special Features	Water and tamper resistant left/center receptacle

### Manufacturer Information

Brand	EATON
GTIN	00786685409542
Manufacturers Part Number	CHR9N9NS
sub brand	None Mount
UPC	786685409542

### Taxonomies, Classifications, and Categories

igcc	4440
Type	Pedestal mount metered
unspsc code	39121310

### Packaging

Carton	1
Weight Per each	30

### Uses, Certifications, and Standards

Mounting	Surface mounting
standard	UL Listed file E163588;UL 231



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Temporary Power/RV Park Pedestal

**CHR9N9NS**

**UPC:**786685409542

### Dimensions:

- **Height:** 31 IN
- **Length:** 7.25 IN
- **Width:** 10 IN

**Weight:**30 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Water and tamper resistant left/center receptacle
- **Type:** Metered-ringless
- **Circuit Breaker Position 1:** Non-ground fault
- **Circuit Breaker Position 3:** None
- **Feed Type:** Top
- **Mounting:** Surface
- **Number Of Circuits:** 4
- **Receptacle Center:** NEMA 5-20R2GF
- **Receptacle Left:** NEMA 5-20R2GFI

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHR9N9NS](#)

### Certifications:

- UL Listed file E163588
- UL 231

**Product compliance:** No Data



