Specifications



Eaton CHSPT2MICRO

SPD Type 2 CHSP Service Entrance Surge Protection, 120/240V line, 150V L-N, 300V L-L MCOV, 600V L-N, 1000V L-L, 800V N-G, 600V L-G VPR, 22 kA SCCR, NEMA 4 enclosure, Single-phase, 60 Hz, 5 kA nominal current discharge, 36 kA surge current

General specifications		
PRODUCT NAME	Eaton CHSPT2 surge protection device	
CATALOG NUMBER	CHSPT2MICRO	
UPC	786685436869	
PRODUCT LENGTH/DEPTH	2.5 in	
PRODUCT HEIGHT	10 in	
PRODUCT WIDTH	3 in	
PRODUCT WEIGHT	1 lb	
CERTIFICATIONS	UL 1449 cUL Certified UL Recognized	
CATALOG NOTES	5kA nominal discharge current. Has 36kA one time surge current rating.	



Product specifications		
FREQUENCY RATING	60 Hz	
INTERRUPT RATING	200 kAIC	
NOMINAL DISCHARGE CURRENT	5 kA	
OPERATING VOLTAGE	150V L-N, 300V L-L	
PROTECTION	600V L-N, 1000V L-L, 800V N-G, 600V L-G	
VOLTAGE RATING	120/240 V	
ENCLOSURE	NEMA 4	
PHASE	Single-phase	
SURGE CURRENT	36 kA	
SHORT-CIRCUIT RATING	22000 kA	
OPERATING TEMPERATURE	-40 to 50 °C	
ТҮРЕ	Surge protection device	
SPECIAL FEATURES	Meets or exceeds the requirments specified in IBC ®2006, CBC2007, and UBC®Zone 4	

Resources	
BROCHURES	Storm season is coming. Are you prepared?
CATALOGS	Residential and Light Commercial, Surge Protection, Volume 1 Tab 2
SPECIFICATIONS AND DATASHEETS	<u>Eaton Specification Sheet -</u> <u>CHSPT2MICRO</u>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland

Eaton.com

 $\hbox{@ 2025 Eaton.}$ All Rights Reserved.

Follow us on social media to get the latest product and support information.









