

Eaton CHT1515

Catalog Number: CHT1515

Eaton CH thermal magnetic circuit breaker, Type CHT twin breaker, 50 A, 10 kAIC, Single-pole, 120/240V, CHT, #14-8 AWG Cu/Al, CHT, Type CH Loadcenters, 50-60 Hz, Switching duty rated, HCAR rated



General specifications

Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CHT1515
	UPC
	782113631530
Product Length/Depth	Product Height
0.7 in	2.6 in
Product Width	Product Weight
3.2 in	0.25 lb
Certifications	
UL Listed	
UL 489	

defaultTaxonomyAttributeLabel

Type

Type CHT twin breaker

Amperage Rating

15-15A

Voltage rating

120/240 V

Circuit breaker type

CH

Frequency rating

50-60 Hz

Used with

Type CH Loadcenters

Mounting Method

Plug-on

Rating

Switching duty rated, HCAR rated

Interrupt rating

10 kAIC

Main circuit breaker

CHT

Wire size

#14-8 AWG Cu/Al

Number of poles

Single-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHT1515](#)