

Eaton CHU1NSFEMA

Catalog Number: CHU1NSFEMA

Eaton pedestal mount unmetered, Unmetered, 50A, None, None, Non-ground fault, None, None, CH, Top, Surface, Circuits: 4, NEMA 14-50R, None, None, 4, 0, 0, 125/250V, None, None

General specifications



Product Name

Eaton pedestal mount unmetered

Catalog Number

CHU1NSFEMA

UPC

782116910205

Product Length/Depth

4.3 in

Product Height

17.1 in

Product Width

9.5 in

Product Weight

8.25 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588
UL 231

Catalog Notes

Replaces CHU1NS.

Type

Unmetered

Receptacle center

None

Receptacle left

NEMA 14-50R

Receptacle right

None

Circuit breaker type

CH

Feed type

Top

Mounting

Surface

Number of circuits

4

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CHU1NSFEMA](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)