

# Eaton CHU2G2GKGS

Catalog Number: CHU2G2GKGS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Ground fault, Ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2 (2), NEMA 5-20R2(2) WR, NEMA 6-20R2(2) WR, 3, 3, 3, 125V, 125V, 250V



## General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU2G2GKGS
UPC	Product Length/Depth
786685948287	6.8 in
Product Height	Product Width
39.9 in	9.5 in
Product Weight	Warranty
15.8 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

## Physical Attributes

[Circuit breaker position 1](#)

Ground fault

[Circuit breaker position 2](#)

Ground fault

[Circuit breaker position 3](#)

Ground fault

[Mounting](#)

Surface

[Receptacle center](#)

NEMA 5-20R2 WR

[Receptacle left](#)

NEMA 5-20R2 WR

[Receptacle right](#)

NEMA 6-20R2 WR

[Type](#)

Unmetered

## Resources

[Specifications and datasheets](#)

[Eaton Specification Sheet - CHU2G2GKGS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CHU2G2GKGS

Catalog Number: CHU2G2GKGS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Ground fault, Ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2 (2), NEMA 5-20R2(2) WR, NEMA 6-20R2(2) WR, 3, 3, 3, 125V, 125V, 250V



## General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU2G2GKGS
UPC	Product Length/Depth
786685948287	6.8 in
Product Height	Product Width
39.9 in	9.5 in
Product Weight	Warranty
15.8 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

## Physical Attributes

[Circuit breaker position 1](#)

Ground fault

[Circuit breaker position 2](#)

Ground fault

[Circuit breaker position 3](#)

Ground fault

[Mounting](#)

Surface

[Receptacle center](#)

NEMA 5-20R2 WR

[Receptacle left](#)

NEMA 5-20R2 WR

[Receptacle right](#)

NEMA 6-20R2 WR

[Type](#)

Unmetered

## Resources

[Specifications and datasheets](#)

[Eaton Specification Sheet - CHU2G2GKGS](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)