

Eaton CHU2G2GKGS

Catalog Number: CHU2G2GKGS

Eaton pedestal mount unmetered, Unmetered, 20A, 20A, 20A, Ground fault, Ground fault, Ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2 (2), NEMA 5-20R2(2) WR, NEMA 6-20R2(2) WR, 3, 3, 125V, 125V, 250V



General specifications

| | |
|--------------------------------|--|
| Product Name | Catalog Number |
| Eaton pedestal mount unmetered | CHU2G2GKGS |
| UPC | Product Length/Depth |
| 786685948287 | 6.8 in |
| Product Height | Product Width |
| 39.9 in | 9.5 in |
| Product Weight | Warranty |
| 15.8 lb | Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. |
| Certifications | |
| UL Listed | |

defaultTaxonomyAttributeLabel

Resources

Type

Unmetered

Circuit breaker position 1

Ground fault

Circuit breaker position 2

Ground fault

Circuit breaker position 3

Ground fault

Receptacle center

NEMA 5-20R2 WR

Receptacle left

NEMA 5-20R2 WR

Receptacle right

NEMA 6-20R2 WR

Mounting

Surface

Specifications and datasheets

[Eaton Specification Sheet - CHU2G2GKGS](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)