

Eaton CHU4N7NS

Catalog Number: CHU4N7NS

Eaton pedestal mount unmetered, Unmetered, 30A, 20A, None, Non-ground fault, Non-ground fault, None, Top, Surface, Circuits: 4, NEMA TT-30R, NEMA 5-20R2GFI, None, 3, 3, 0, 125V, 125V, None



General specifications

Product Name	Catalog Number
Eaton pedestal mount unmetered	CHU4N7NS
UPC	Product Length/Depth
782114203743	13.6 in
Product Height	Product Width
39.9 in	9.5 in
Product Weight	Warranty
8.6 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588
UL 231

defaultTaxonomyAttributeLabel

Type

Unmetered

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

None

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA TT-30R

Receptacle right

None

Feed type

Top

Mounting

Surface

Number of circuits

4

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - POWER OUTLET, SURFACE MOUNT, UNMETERED

Specifications and datasheets

Eaton Specification Sheet - CHU4N7NS



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia